



# BB300L6000 Flexible Copper Braid

By Burndy  
Catalog # [BB300L6000](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

Standards - RoHS Compliance    CM  
Status

## Configuration

Connector Type                      Braid

## Dimensions

Length                                      6000 in  
Dimension - L Length Overall        152400 mm  
mm  
Dimension - Length Overall            6000 in  
inch

## General

UPC                                          781810460054  
Material                                  Copper  
UPC 12 Digit                              781810460054  
UPC 14 Digit GTIN                      00781810460054

## Logistics

Minimum Pack Quantity                1

## Product Assets

[Catalog \[English\]](#)