



# BB300L720 Flexible Copper Braid

By Burndy  
Catalog # [BB300L720](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | EX |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |

Certification - CSA Approved      No

## Configuration

Connector Type      Braid

## Dimensions

|                              |          |
|------------------------------|----------|
| Length                       | 720 in   |
| Dimension - L Length Overall | 18288 mm |
| mm                           |          |
| Dimension - Length Overall   | 720 in   |
| inch                         |          |

## General

|                   |                |
|-------------------|----------------|
| UPC               | 781810205679   |
| Material          | Copper         |
| UPC 12 Digit      | 781810205679   |
| UPC 14 Digit GTIN | 00781810205679 |

## Logistics

Minimum Pack Quantity      1

## Product Assets

[Catalog \[English\]](#)