



BB403L25D50G2TN Flexible Copper Braid

By Burndy
Catalog # [BB403L25D50G2TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No

Certification - CSA Approved No

Configuration

Connector Type Braid

Dimensions

Length	25.5 in
Dimension - L Length Overall mm	647 mm
Dimension - Length Overall inch	25.50 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810174753
Material	Copper
UPC 12 Digit	781810174753
UPC 14 Digit GTIN	00781810174753

Product Assets

[Catalog \[English\]](#)