



BBB14224B, Bare Copper Busbar, 24" Long, 36 Holes

By Burndy
Catalog # [BBB14224B](#)

Copper Busbar, 36 Holes, 24 in L, Can be used as a common ground point and power applications

Features

- Bare Copper Busbar
- UL Listed for Grounding
- Many sizes and hole patterns available

Application

For Used As A Common Ground Point And Power Applications

Specifications

Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No

Configuration

Physical Attribute - Number of Holes	36
--------------------------------------	----

Dimensions

Dimension - Bar Width inch	2 in
----------------------------	------



Dimension - Bar Thickness mm	6 mm
Dimension - Bar Width mm	51 mm
Dimension - Bar Thickness inch	0.25 in
Dimension - Width inch	2.00 in
Dimension - Bar Length mm	610 mm
Dimension - Bar Length inch	24 in
Dimension - Width fraction	2 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in

General

Sub Brand	BUS BAR
UPC	781810489321
Type	BBB
Material	Copper
UPC 12 Digit	781810489321
UPC 14 Digit GTIN	00781810489321

Logistics

Minimum Pack Quantity	1
Pallet Quantity	90
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)