



BC28, Copper Deadend Clamp for Guy Wire, 2/0 Str - 4/0 Str

By Burndy
Catalog # [BC28](#)



Copper Deadend Clamp for Guy Wire, 2/0 Stranded - 4/0 Stranded, supplied with silicon bronze U-bolt, nuts and washers

Features

- Supplied with silicon bronze U-bolt, nuts, and washers
- Saddle is made of high strength, corrosion resistant copper alloy

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Dimension - Pin Diameter inch	0.50 in
Dimension - Pin Diameter fraction	1/2 in
Dimension - Pad Width inch	1.13 in
Package Height	0.000 in

Dimension - Height mm	60.3 mm
Dimension - Height inch	2.375 in
Dimension - Height fraction	2-3/8 in
Dimension - B Length fraction	1-5/8 in
Package Weight	0.000 lb.
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	44 mm
Dimension - B Length inch	1.63 in
Dimension - Width fraction	2-1/4 in
Dimension - Length Overall inch	1.75 in

General

Plated	N
UPC	781810013496
Prefilled Oxide Inhibitor	N
Material	Copper Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810013496

Logistics

Minimum Pack Quantity	10
Pallet Quantity	432
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)