



BC30, Cu Deadend, 4/0 Str - 300 kcmil, 5/8" Guy Wire

By Burndy
Catalog # [BC30](#)

Copper Dead End Clamp for 4/0 AWG Stranded to 300 kcmil Copper; 5/8" Guy Wire



Features

- Supplied with silicon bronze U-bolt, nuts, and washers
- Saddle is made of high strength, corrosion resistant copper alloy

Specifications

Certification - CSA Approved	No
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX

Conductor

Conductor Range	#4/0 AWG (Str) - 300 kcmil
-----------------	----------------------------

Dimensions

Package Length	0.000 in
Dimension - Bolt Size inch	3/8 in

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - D inch	1.19 in
Package Height	0.000 in

General

U Bolt Type	UB226
Material	Copper Alloy, Cast
UPC	781810891001
Plated	N

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)