



Black Cold Shrink, 6" Long, Jacket OD Range: .39"-.80"

By Burndy
Catalog # [BCSC110600](#)

Black Cold Shrink Sleeve, 6" Long, Jacket OD Range: .39"-.80" , , factory expanded over removable plastic ripcord housing

Features

- Length of tube is consistent before and after application
- Easy, safe installation
- Suitable for wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip Installation does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable

Application

Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems

Current



Voltage Rating	2000 V
Dimensions	
Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
General	
Product Type	Black Cold Shrink
Color	Black
UPC	621945667402
Material	Silicone Rubber
Logistics	
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)