



BD10G262 Flex Cu Braid, Cu Ferrules,
10.00"x0.28"x0.19"

By Burndy
Catalog # [BD10G262](#)

Flexible copper Braid, Copper Ferrules 10.00"x0.28"x0.19"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Package Height	0.000 in
Length	10 in
Package Weight	0.000 lb.
Dimension - Width inch	0.28
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	254
Height	0.19 in
Width	0.28 in
Dimension - Length Overall inch	10
Dimensions	10 in x 0.28 in x 0.19 in

General

UPC	781810503744
Material	Copper
UPC 12 Digit	781810503744
UPC 14 Digit GTIN	00781810503744

Logistics

Minimum Pack Quantity	500
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)