

BD12N 12 inch Flexible Copper Braid

By Burndy
Catalog # [BD12N](#)

12 inch Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190
--------------------------	-----

Rating - Outdoor Amperage	225
---------------------------	-----

Dimensions

Dimension - Pad Width inch	0.94 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Width	0.94 in
Dimension - Hole Size inch	0.56 in
Length	12 in
Height	0.13 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	12 in
Dimensions	12 in x 0.94 in x 0.13 in

General

Material - Ferrules Plated	Y
Physical Attribute - Number of Braids	1
Sub Brand	BRAID
UPC	781810807033
Type	B, Flexible
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810807033
UPC 14 Digit GTIN	00781810807033

Logistics

Pallet Quantity	3500
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)