



BD12N1TN 12 inch Flexible Copper Braid

By Burndy
Catalog # [BD12N1TN](#)

12 inch Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Dimensions

Length	12 in
Dimension - L Length Overall	305 mm
mm	
Dimension - Length Overall	12 in
inch	

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810218754
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810218754
UPC 14 Digit GTIN	00781810218754

Logistics

Pallet Quantity	5250
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)