



BD12NB 12 inch Flexible Copper Braid

By Burndy
Catalog # [BD12NB](#)

12 inch Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Rope lay
----------------	----------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Package Height	0.000 in
Length	12 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	305 mm
mm	
Dimension - Length Overall	12 in
inch	

General

UPC	781810674987
Material	Copper
UPC 12 Digit	781810674987
UPC 14 Digit GTIN	00781810674987

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand