



BD15G92W15 Flexible Copper Braid, 15" Long

By Burndy
Catalog # [BD15G92W](#)

15 inch Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Length	15 in
Dimension - Length Overall	15 in
inch	
Dimension - L Length Overall	381 mm
mm	

General

Plated	Y
UPC	621945468726
Material	Copper

Logistics

Pallet Quantity	4800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)