



# BD18G127 18 inch Flexible Copper Braid

By Burndy  
Catalog # [BD18G127](#)

18 inch Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                |       |
|--------------------------------|-------|
| Standards - Industry Standards | UL467 |
| Met                            |       |
| Standards - RoHS Compliance    | NC    |
| Status                         |       |
| Industry Standard(s)           | UL467 |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 190 |
| Rating - Outdoor Amperage | 225 |

## Dimensions

|                              |           |
|------------------------------|-----------|
| Package Height               | 0.000 in  |
| Length                       | 18 in     |
| Package Weight               | 0.000 lb. |
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Dimension - L Length Overall | 457 mm    |
| mm                           |           |
| Dimension - Length Overall   | 18.00 in  |
| inch                         |           |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | N              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810443057   |
| Material                              | Copper         |
| Plating Type                          | Tin            |
| UPC 12 Digit                          | 781810443057   |
| UPC 14 Digit GTIN                     | 00781810443057 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 1 |

## Product Assets

[Catalog \[English\]](#)