



BD24G272TN Tin Plated Copper Braid 24 in Long

By Burndy
Catalog # [BD24G272TN](#)

Tin Plated Copper Braid 24 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes

Certification - CSA Approved Yes

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Length	24 in
Dimension - L Length Overall	610 mm
Dimension - Length Overall	24.00 in

General

UPC	781810567401
Material	Copper
UPC 12 Digit	781810567401
UPC 14 Digit GTIN	00781810567401

Product Assets

[Catalog \[English\]](#)