



BD30G158 Flexible Copper Braid 30 in Long

By Burndy
Catalog # [BD30G158](#)

Flexible Copper Braid 30 in Long.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BD30G158
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810217023
UPC 14 Digit GTIN	00781810217023

Dimensions



Dimension - L Length Overall	762 mm
mm	
Dimension - Length Overall	30.00 in
inch	
Length	30 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Grounding Braid Product Guide](#)
- [Sales Drawings - 10060680-01_A1](#)
- [Specifications - BD30G158 Specification Sheet English](#)
- [Specifications - BD30G158 Specification Sheet French](#)