



BD33D46G261TN Tin Plated Copper Braid 33.46 in Long

By Burndy
Catalog # [BD33D46G261TN](#)

Tin Plated Copper Braid 33.46 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Length	33.46 in
Dimension - L Length Overall mm	850 mm
Dimension - Length Overall inch	33.46 in

General

Plated	Y
Physical Attribute - Number of Braids	1
UPC	781810497531
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810497531
UPC 14 Digit GTIN	00781810497531

Product Assets

[Catalog \[English\]](#)