



BD34 Flexible Copper Braid 34 in Long

By Burndy
Catalog # [BD34](#)

Flexible Copper Braid 34 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
--------------------------	-------

Rating - Outdoor Amperage	225 A
---------------------------	-------

Dimensions

Package Height	0.000 in
Length	34 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	864 mm
Height	0.13 in
Width	0.94 in
Dimension - Length Overall inch	34.00 in
Dimensions	34 in x 0.94 in x 0.13 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810201770
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810201770
UPC 14 Digit GTIN	00781810201770

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)