



BD58D75G285TN Tin Plated Copper Braid 58.75 in Long

By Burndy
Catalog # [BD58D75G285TN](#)

Tin Plated Copper Braid 58.75 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Package Height	0.000 in
Length	58.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	1492 mm
mm	
Dimension - Length Overall	58.75 in
inch	

General

UPC	621945431324
Material	Copper
UPC 12 Digit	621945431324
UPC 14 Digit GTIN	00621945431324

Logistics

Minimum Pack Quantity	1
Pallet Quantity	840
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)