



# BD6 Flexible Copper Braid 6 in Long

By Burndy  
Catalog # [BD6](#)

Flexible Copper Braid 6 in Long



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| UL Listed                          | Yes   |
| Certification - CSA Approved       | Yes   |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                          |       |
|--------------------------|-------|
| Rating - Indoor Amperage | 190 A |
|--------------------------|-------|

|                           |       |
|---------------------------|-------|
| Rating - Outdoor Amperage | 225 A |
|---------------------------|-------|

## Dimensions

|                                 |                          |
|---------------------------------|--------------------------|
| Package Height                  | 0.000 in                 |
| Length                          | 6 in                     |
| Package Weight                  | 0.000 lb.                |
| Package Length                  | 0.000 in                 |
| Package Width                   | 0.000 in                 |
| Dimension - L Length Overall mm | 152 mm                   |
| Height                          | 0.13 in                  |
| Width                           | 0.94 in                  |
| Dimension - Length Overall inch | 6.00 in                  |
| Dimensions                      | 6 in x 0.94 in x 0.13 in |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | Y              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810349151   |
| Material                              | Copper         |
| Plating Type                          | Tin            |
| UPC 12 Digit                          | 781810349151   |
| UPC 14 Digit GTIN                     | 00781810349151 |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 8400 |
| Carton Quantity       | 50   |

## Product Assets

[Catalog \[English\]](#)