



BD6T14 Flexible Copper Braid 6 in Long

By Burndy
Catalog # [BD6T14](#)

Flexible Copper Braid 6 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Length	6 in
Dimension - L Length Overall	152 mm
Dimension - N inch	0.5 in
Dimension - Length Overall	6.00 in
inch	
Dimension - Stud Size inch	1/4

General

Physical Attribute - Number of Braids	1
UPC	781810552643
Material	Copper
UPC 12 Digit	781810552643
UPC 14 Digit GTIN	00781810552643

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)