



# BD70TN Flexible Copper Braid

By Burndy  
Catalog # [BD70TN](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| UL Listed                          | Yes   |
| Certification - CSA Approved       | Yes   |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 190 |
| Rating - Outdoor Amperage | 225 |

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Length                          | 70 in     |
| Package Weight                  | 0.000 lb. |
| Dimension - Width mm            | 24 mm     |
| Dimension - Width inch          | 0.94      |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 1778      |
| Dimension - Length Overall inch | 70        |

## General

|                                       |                   |
|---------------------------------------|-------------------|
| Plated                                | Y                 |
| Material - Ferrules                   | Tin Plated Copper |
| Physical Attribute - Number of Braids | 1                 |
| UPC                                   | 781810496381      |
| Material                              | Copper            |
| Plating Type                          | Tin               |
| UPC 12 Digit                          | 781810496381      |
| UPC 14 Digit GTIN                     | 00781810496381    |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 4 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 1 |

## Product Assets

[Catalog \[English\]](#)