



BD72N Flexible Copper Braid 72 in Long

By Burndy
Catalog # [BD72N](#)

Flexible Copper Braid 72 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Length	72 in
Dimension - L Length Overall	1829 mm
mm	
Height	0.13 in
Width	0.94 in
Dimension - Length Overall	72.00 in
inch	
Dimensions	72 in x 0.94 in x 0.13 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810082720
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810082720
UPC 14 Digit GTIN	00781810082720

Logistics

Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)