



BD7D75G281 Flexible Copper Braid 7.75 in Long

By Burndy
Catalog # [BD7D75G281](#)

Flexible Copper Braid 7.75 in Long



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
Current	
Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A
Dimensions	
Length	7.75 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
General	
UPC	781810656303
Material	Copper
UPC 12 Digit	781810656303
UPC 14 Digit GTIN	00781810656303
Logistics	
Minimum Pack Quantity	1
Pallet Quantity	6300
Carton Quantity	50
Product Assets	
Catalog [English]	