




BDBLCS3A1FSKIT, Power Distribution Block Finger Safe Kit

By Burndy
Catalog # [BDBLCS3A1FSKIT](#)



FINGER-SAFE KIT.

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - cULus	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	VERSIPOLE™
UPC	621945450240
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	621945450240
UPC 14 Digit GTIN	00621945450240

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	20

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

[Catalog \[English\]](#)



A Hubbell brand