



BURNDY

BDBLHC2125002, 2-Pole Power Distribution Block

By Burndy

Catalog # [BDBLHC2125002](#)

Aluminum Power Distribution Block, 2 Pole, Run: #6 AWG - 350 kcmil, Tap: #14 - 4 AWG, 760 Amp/Pole



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL

No
Certification - UL Recognized
No
Standards - RoHS Compliance Status
CM
Certification - cULus
No
UL Listed
Yes
Certification - CSA Approved
Yes

Conductor

Conductor - Copper Str Run Range
4-500
Conductor - Copper Str Run

- 4
- 3
- 2
- 1
- 1/0
- 2/0
- 3/0
- 4/0
- 250
- 300
- 350
- 400
- 450
- 500

Number Of Poles
2
Conductor - AL Str Run Range
4-500
Conductor - AL Str Run

- 4
- 3
- 2
- 1
- 1/0
- 2/0
- 3/0
- 4/0
- 250
- 266.8
- 300
- 336.4
- 350
- 397.5
- 400
- 450
- 477
- 500

Conductor - AL Str Tap Range
14-4
Conductor - AL Str Tap

- 12
- 10
- 8
- 6
- 4

Conductor Type

- AL C Str-Run
- CU C Str-Run
- AL C Str-Tap
- CU C Str-Tap

Conductor - Copper Str Tap Range
14-4
Conductor - Copper Str Tap

- 14
- 12
- 10

- 9
- 8
- 7
- 6
- 5
- 4

Current

Amperage Rating
760 A
Rating - Minimum Voltage
600

Dimensions

Package Height
0.000 in
Dimension - Height mm
90.2 mm
Length
5.31 in
Dimension - Height inch
3.55
Package Weight
0.000 lb.
Dimension - Width mm
145 mm
Dimension - Width inch
5.70 in
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
135
Height
3.55 in
Width
4.75 in
Dimension - Length Overall inch
5.73
Dimensions
5.31 in x 4.75 in x 3.55 in

General

Plated
Y
Trade Name
VERSIPOLE™
UPC
781810646588
Insulation
Y
Material
Aluminum
Plating Type
Tin
UPC 12 Digit
781810646588
UPC 14 Digit GTIN
00781810646588

Logistics

Minimum Pack Quantity
1
Pallet Quantity
480
Carton Quantity
9

Operational

Temperature Rating
194° F

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-BDBLHC2125002-SPEC-EN | REV 5/2026