



BDBMCS3SM3, Flex Rated Stud Style Power Distribution Block

By Burndy

Catalog # **BDBMCS3SM3**

Aluminum Power Distribution Block, 3 Pole, Run: 3/8" Stud, Tap:
#14 - 2/0 AWG (B,C,H,I,K, DLO), 420 Amp/Pole

Features

- 600 Volt Rated
- Listed to UL1953
- Rated for use with code and flex conductor without requiring ferrules
- AL9CU dual rated for use with copper and aluminum conductors
- Range taking conductor ports can accommodate wire sizes up to 535 DLO and can support up to 5 run conductors and up to 24 tap conductors
- High Short-Circuit Current Rating up to 100kA with proper fusing

Specifications

Standards - RoHS Compliance	CM
Status	



Dimensions

Weight 1.77 lb.

General

Material	Aluminum
UPC	621945518858
Trade Name	VERSIPOLE™

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand