



BDBMHC113503, 3-Pole Power Distribution Block

By Burndy
Catalog # BDBMHC113503



Power Distribution Block, Glass Filled Polycarbonate, AWG 6 - 350 kcmil (Run), AWG 6 - 350 kcmil (Tap)

Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Application

Industrial control feeder, HVAC system and wire ways

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	6-350
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor - AL Str Tap Range	6-350
Conductor - AL Str Tap	• 6 • 4 • 3 • 2 • 1 • 1/0

	• 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Run	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350
Number Of Poles	3
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	6-350
Conductor - Copper Str Tap	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350

Current

Amperage Rating	310 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Dimension - Height inch	3.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Width	3.88 in
Length	5.28 in
Dimension - Width mm	134 mm
Dimension - Width inch	5.28 in
Height	3.25 in
Dimension - Length Overall inch	5.00 in
Dimensions	5.28 in x 3.88 in x 3.25 in

General

Product Family	Power Connectors>Power Distribution Blocks
Trade Name	VERSIPOLE™
Insulation	Y



A Hubbell brand

Plated	Yes
Sub Brand	VERSI-POLE
Product Type	Mechanical
UPC	781810645727
Type	BDB
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810645727
UPC 14 Digit GTIN	00781810645727

Logistics

Minimum Pack Quantity	1
Pallet Quantity	676
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)