



BDBMHC222/03, 3-Pole Power Distribution Block

By Burndy
Catalog # BDBMHC222/03

Aluminum Power Distribution Block, 3 Pole, Run and Tap: #14 - 2/0
AWG, 350 Amp/Pole



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Application

Suitable for use with aluminum or copper conductors providing maximum versatility

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Run	• 12 • 10 • 8 • 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - AL Str Tap Range	12-2/0
Conductor - AL Str Tap	• 12 • 10 • 8 • 6 • 4 • 3 • 2 • 1

	• 1/0 • 2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Run	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Number Of Poles	3
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	14-2/0
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0

Current

Amperage Rating	350 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Dimension - Height inch	3.25 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Width	3.88 in
Length	5.28 in
Dimension - Width mm	134 mm
Dimension - Width inch	5.28 in
Height	3.25 in
Dimension - Length Overall inch	5.00 in
Dimensions	5.28 in x 3.88 in x 3.25 in

General

Product Family	Power Connectors>Power Distribution Blocks
Trade Name	VERSIPOLE™
Insulation	Y
Plated	Yes
Sub Brand	VERSIPOLE



A Hubbell brand

Product Type	Mechanical
UPC	781810645925
Type	BDBMH
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810645925
UPC 14 Digit GTIN	00781810645925

Logistics

Minimum Pack Quantity	1
Pallet Quantity	624
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)