



# BDBSCSCOVER, Power Distribution Block Cover

By Burndy  
Catalog # [BDBSCSCOVER](#)

Polycarbonate Cover for Small Size BDBSCS Style Power Distribution Blocks

## Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

## Application

For Use On: Suitable for use with aluminum or copper conductors

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Standards - RoHS Compliance Status | CM                   |
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | Yes                  |
| EU RoHS Indicator                  | Yes                  |
| Buy America(n) Qualified           | Contact Manufacturer |
| Certification - CSA Approved       | No                   |

## Conductor

|                |                                                                                                                                     |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Type | <ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul> |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------|

## Configuration



Connector Type                      Power Distribution Block

## Current

Rating - Minimum Voltage                      600

## Dimensions

|                       |           |
|-----------------------|-----------|
| Package Height        | 0.000 in  |
| Dimension - Height mm | 0 mm      |
| Package Weight        | 0.000 lb. |
| Package Length        | 0.000 in  |
| Package Width         | 0.000 in  |

## General

|                   |                       |
|-------------------|-----------------------|
| Plated            | Y                     |
| Trade Name        | VERSIPOLE™            |
| Sub Brand         | VERSI-POLE            |
| UPC               | 621945449343          |
| Type              | Terminal Block Covers |
| Insulation        | Y                     |
| Material          | Aluminum              |
| Plating Type      | Tin                   |
| UPC 12 Digit      | 621945449343          |
| UPC 14 Digit GTIN | 00621945449343        |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1     |
| Pallet Quantity       | 45000 |
| Carton Quantity       | 300   |

## Operational

Temperature Rating                      194

## Product Assets

[Catalog \[English\]](#)