



# BE10NSV Flexible Copper Braid

By Burndy  
Catalog # [BE10NSV](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                         |     |
|-----------------------------------------|-----|
| Certification - CSA Approved            | Yes |
| UL Listed                               | Yes |
| Certification - UL Listed Direct Burial | No  |
| Standards - RoHS Compliance Status      | CM  |

## Current

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 340 |
| Rating - Outdoor Amperage | 405 |

## Dimensions

|                                 |                          |
|---------------------------------|--------------------------|
| Dimension - Width inch          | 1.5                      |
| Dimension - Width mm            | 38 mm                    |
| Dimension - L Length Overall mm | 305                      |
| Dimension - Length Overall inch | 12                       |
| Width                           | 1.5 in                   |
| Height                          | 0.17 in                  |
| Length                          | 10 in                    |
| Dimensions                      | 10 in x 1.5 in x 0.17 in |

## General

|                     |                   |
|---------------------|-------------------|
| Material - Ferrules | Tin Plated Copper |
| UPC                 | 621945471108      |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 25  |
| Carton Quantity       | 10  |
| Pallet Quantity       | 900 |

## Product Assets

[Catalog \[English\]](#)