



BE12N Flexible Copper Braid, 2-Ferrule, 2-Hole, 12" Length

By Burndy
Catalog # [BE12N](#)

Flexible Copper Braid Jumper, 2 Ferrules, 2 Hole, 1.75" Spacing, 12" Length

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Application

For Use On: Designed to take up linear expansion and contraction, compensate for misalignment and absorb vibratory movement of electrical equipment and devices

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405



Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Width	1.5 in
Dimension - Hole Size inch	0.56 in
Length	12 in
Height	0.17 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	12.00 in
Dimensions	12 in x 1.5 in x 0.17 in

General

Product Family	Grounding and Bonding Connectors>Braid, Jumpers, Shunts>Braid Shunts
Material - Ferrules	Y
Plated	Yes
Physical Attribute - Number of Braids	1
Sub Brand	BRAID JUMPER
Product Type	Mechanical
UPC	781810005132
Type	B, Flexible
Construction Material - Main Material	Copper
UPC 12 Digit	781810005132
UPC 14 Digit GTIN	00781810005132

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1100
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)