



BE14D50N Flexible Copper Braid

By Burndy
Catalog # [BE14D50N](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
Current	
Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405
Dimensions	
Length	14.5 in
Dimension - L Length Overall	368 mm
Height	0.17 in
Width	1.5 in
Dimension - Length Overall	14.50 in
Dimensions	14.5 in x 1.5 in x 0.17 in
General	
Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810145166
Material	Copper
UPC 12 Digit	781810145166
UPC 14 Digit GTIN	00781810145166

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)