



BE18D58G170TN Flexible Copper Braid

By Burndy
Catalog # [BE18D58G170TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes

Certification - CSA Approved Yes

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage 340 A
Rating - Outdoor Amperage 405 A

Dimensions

Length 18.58 in
Dimension - Width mm 30 mm
Dimension - Width inch 1.2
Dimension - L Length Overall mm 472
Dimension - Length Overall inch 18.58

General

Material - Ferrules Tin Plated Copper
Physical Attribute - Number of Braids 1
UPC 781810493694
Material Copper
UPC 12 Digit 781810493694
UPC 14 Digit GTIN 00781810493694

Product Assets

[Catalog \[English\]](#)