



BE18D63TNCG1 Flexible Copper Braid

By Burndy
Catalog # BE18D63TNCG1

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Dimensions

Package Height	0.000 in
Length	18.63 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.5
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	462 mm
Weight	0.87 lb.
Dimension - Length Overall inch	18.20 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810420980
Material	Copper
UPC 12 Digit	781810420980
UPC 14 Digit GTIN	00781810420980

Logistics

Pallet Quantity	576
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)