



# BE18G218TN Flexible Copper Braid

By Burndy  
Catalog # BE18G218TN

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliance   | CM  |
| Status                        |     |
| Certification - cULus         | No  |
| UL Listed                     | Yes |
| Certification - CSA Approved  | Yes |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |       |
|---------------------------|-------|
| Rating - Indoor Amperage  | 340 A |
| Rating - Outdoor Amperage | 405 A |

## Dimensions

|                              |           |
|------------------------------|-----------|
| Package Height               | 0.000 in  |
| Length                       | 18 in     |
| Package Weight               | 0.000 lb. |
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Dimension - L Length Overall | 457 mm    |
| mm                           |           |
| Dimension - Length Overall   | 18.00 in  |
| inch                         |           |

## General

|                   |                |
|-------------------|----------------|
| UPC               | 781810665794   |
| Material          | Copper         |
| UPC 12 Digit      | 781810665794   |
| UPC 14 Digit GTIN | 00781810665794 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)