



BE18NTN Flexible Copper Braid

By Burndy
Catalog # BE18NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
Industry Standard(s)	UL467
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
Dimensions	
Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	457 mm
mm	
Height	0.17 in
Width	1.5 in
Dimension - Length Overall	18.00 in
inch	
Dimensions	18 in x 1.5 in x 0.17 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of	1
Braids	
UPC	781810472637
Material	Copper
UPC 12 Digit	781810472637
UPC 14 Digit GTIN	00781810472637

Product Assets

[Catalog \[English\]](#)