



BE18T38G219TN Flexible Copper Braid

By Burndy
Catalog # BE18T38G219TN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	457 mm
mm	
Weight	2.614 lb.
Dimension - Length Overall	18 in
inch	

General

UPC	621945460027
Material	Copper
UPC 12 Digit	621945460027
UPC 14 Digit GTIN	00621945460027

Logistics

Minimum Pack Quantity	25
Pallet Quantity	975
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)