



BE36TN Flexible Copper Braid

By Burndy
Catalog # [BE36TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct	No
Burial	

Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	36 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945432109
Material	Copper
UPC 12 Digit	621945432109
UPC 14 Digit GTIN	00621945432109

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)