



# BE37D50G42 Flexible Copper Braid

By Burndy  
Catalog # [BE37D50G42](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - ETL                     | No    |
| Certification - UL Recognized           | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | NC    |
| Certification - cULus                   | No    |
| Certification - UL Listed Direct Burial | No    |
| Industry Standard(s)                    | UL467 |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | Yes   |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 340 |
| Rating - Outdoor Amperage | 405 |

## Dimensions

|                              |                            |
|------------------------------|----------------------------|
| Package Height               | 0.000 in                   |
| Length                       | 37.5 in                    |
| Package Weight               | 0.000 lb.                  |
| Package Length               | 0.000 in                   |
| Package Width                | 0.000 in                   |
| Dimension - L Length Overall | 953 mm                     |
| mm                           |                            |
| Height                       | 0.17 in                    |
| Width                        | 1.5 in                     |
| Dimension - Length Overall   | 37.50 in                   |
| inch                         |                            |
| Dimensions                   | 37.5 in x 1.5 in x 0.17 in |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | Y              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810442432   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810442432   |
| UPC 14 Digit GTIN                     | 00781810442432 |

## Logistics

|                 |     |
|-----------------|-----|
| Pallet Quantity | 160 |
| Carton Quantity | 10  |

## Product Assets

[Catalog \[English\]](#)