



BE60N Flexible Copper Braid

By Burndy
Catalog # BE60N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	340 A
--------------------------	-------

Rating - Outdoor Amperage	405 A
---------------------------	-------

Dimensions

Package Height	0.000 in
Length	60 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.5
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	1524
Height	0.17 in
Width	1.5 in
Dimension - Length Overall inch	60
Dimensions	60 in x 1.5 in x 0.17 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	621945431881
Material	Copper
UPC 12 Digit	621945431881
UPC 14 Digit GTIN	00621945431881

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)