



# BF16G81W Flexible Copper Braid

By Burndy  
Catalog # [BF16G81W](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
  - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
  - Braid is especially suited for applications that require flexibility or resistance to vibration
  - Extra fine stranding gives enhanced flexibility
  - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
  - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
  - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - ETL                     | No    |
| Certification - UL Recognized           | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| Certification - cULus                   | No    |
| Certification - UL Listed Direct Burial | No    |
| Industry Standard(s)                    | UL467 |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | Yes   |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                              |           |
|------------------------------|-----------|
| Package Height               | 0.000 in  |
| Length                       | 16 in     |
| Package Weight               | 0.000 lb. |
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Dimension - L Length Overall | 406 mm    |
| Dimension - Length Overall   | 16.00 in  |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | Y              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810478479   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810478479   |
| UPC 14 Digit GTIN                     | 00781810478479 |

## Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 24 |
| Pallet Quantity       | 1  |
| Carton Quantity       | 1  |

## Product Assets

[Catalog \[English\]](#)