



# BF18N Flexible Copper Braid

By Burndy  
Catalog # BF18N

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

## Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Certification - ETL                     | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| Certification - UL Listed Direct Burial | No    |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | Yes   |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 360 |
| Rating - Outdoor Amperage | 430 |

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 1.19 in   |
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 457 mm    |
| Dimension - Hole Size inch      | 0.56 in   |
| Length                          | 18 in     |
| Dimension - D inch              | 3.00 in   |
| Dimension - N inch              | 0.62 in   |
| Dimension - Length Overall inch | 18.00 in  |

## General

|                                       |                |
|---------------------------------------|----------------|
| Material - Ferrules                   | Y              |
| Plated                                | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810005255   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810005255   |
| UPC 14 Digit GTIN                     | 00781810005255 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 5 |

## Product Assets

[Catalog \[English\]](#)