



BURNDY

BF24 Flexible Copper Braid

By Burndy
Catalog # [BF24](#)
Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - UL Recognized

No
Certification - cULus
No
Industry Standard(s)
UL467
Certification - ETL
No
Standards - Industry Standards Met
UL467
Standards - RoHS Compliance Status
CM
Certification - UL Listed Direct Burial
No
UL Listed
Yes
Certification - CSA Approved
Yes

Configuration

Connector Type
Braid

Current

Rating - Indoor Amperage
360
Rating - Outdoor Amperage
430

Dimensions

Dimension - Pad Width inch
1.19 in
Package Height
0.000 in
Package Weight
0.000 lb.
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
610 mm
Dimension - Hole Size inch
0.44 in
Length
24 in
Dimension - D inch
3.00 in
Dimension - N inch
0.75 in
Dimension - Length Overall inch
24.00 in

General

Material - Ferrules
Y
Plated
Y
Physical Attribute - Number of Braids
1
UPC
781810005309
Material
Copper
UPC 12 Digit
781810005309
UPC 14 Digit GTIN
00781810005309

Logistics

Minimum Pack Quantity
1
Pallet Quantity
1

Carton Quantity
20

Product Assets

[Catalog \(English\)](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-BF24-SPEC-EN | REV 5/2026