



BF30NTN Flexible Copper Braid

By Burndy
Catalog # [BF30NTN](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BF30NTN
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810485965
UPC 14 Digit GTIN	00781810485965

Dimensions

Dimension - D inch	3 in
Dimension - Hole Size inch	0.56 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.19 in
Length	30 in

Certifications And Compliance

Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1
Minimum Pack Quantity	3

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10101761](#)
[Specifications - BF30NTN](#)