



# BF33D50G87TN Flexible Copper Braid

By Burndy  
Catalog # BF33D50G87TN

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                              |     |
|------------------------------|-----|
| Standards - RoHS Compliance  | UI  |
| Status                       |     |
| UL Listed                    | Yes |
| Certification - CSA Approved | Yes |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |       |
|---------------------------|-------|
| Rating - Indoor Amperage  | 360 A |
| Rating - Outdoor Amperage | 430 A |

## Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Pad Width inch      | 1.19 in  |
| Length                          | 33.5 in  |
| Dimension - L Length Overall mm | 851 mm   |
| Dimension - D inch              | 1.50 in  |
| Dimension - N inch              | 0.75 in  |
| Dimension - Hole Size inch      | 0.56 in  |
| Dimension - Length Overall inch | 33.50 in |

## General

|                   |                |
|-------------------|----------------|
| UPC               | 781810537909   |
| Material          | Copper         |
| UPC 12 Digit      | 781810537909   |
| UPC 14 Digit GTIN | 00781810537909 |

## Product Assets

[Catalog \[English\]](#)