



BF36 Flexible Copper Braid

By Burndy
Catalog # BF36

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Dimensions

Dimension - Pad Width inch	1.19 in
Length	36 in
Dimension - L Length Overall mm	914 mm
Dimension - D inch	3 in
Dimension - N inch	0.75 in
Dimension - Hole Size inch	0.44 in
Dimension - Length Overall inch	36.00 in

General

Plated	N
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810200889
Material	Copper
UPC 12 Digit	781810200889
UPC 14 Digit GTIN	00781810200889

Logistics

Minimum Pack Quantity	1
Pallet Quantity	750
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)