



BF36N2U BF Type Braid, 36" Undrilled

By Burndy
Catalog # [BF36N2U](#)

BF Type Braid, 36" Undrilled



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved Yes

Dimensions

Length 36 in

General

UPC 621945485174

Logistics

Minimum Pack Quantity 1
Carton Quantity 5
Pallet Quantity 450

Product Assets

[Catalog \[English\]](#)