



BF6T716 Flexible Copper Braid

By Burndy
Catalog # BF6T716

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	152 mm
Dimension - D inch	1.50 in
Dimension - N inch	0.75 in
Dimension - Hole Size inch	0.50 in
Dimension - Length Overall inch	6 in

General

UPC	621945431577
Material	Copper
UPC 12 Digit	621945431577
UPC 14 Digit GTIN	00621945431577

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1480
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)