



BF72N Flexible tinned copper braid

72.00"x0.62"x0.25"

By Burndy
Catalog # [BF72N](#)

Flexible tinned copper braid 72.00"x0.62"x0.25"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Dimensions

Length	72 in
Dimension - Width mm	16 mm
Dimension - Width inch	0.62
Dimension - L Length Overall mm	1829
Height	0.5 in
Width	0.62 in
Dimension - Length Overall inch	72.00
Dimensions	72 in x 0.62 in x 0.5 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810654989
Material	Copper
UPC 12 Digit	781810654989
UPC 14 Digit GTIN	00781810654989

Logistics

Minimum Pack Quantity	1
Pallet Quantity	90
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)