



BF8CG5W Flexible Copper Braid

By Burndy
Catalog # [BF8CG5W](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	360
--------------------------	-----

Rating - Outdoor Amperage	430
---------------------------	-----

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Length	8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	203 mm
Height	0.25 in
Width	1.19 in
Dimension - N inch	0.56 in
Dimension - Hole Size inch	0.44 in
Dimension - Length Overall inch	8.00 in
Dimensions	8 in x 1.19 in x 0.25 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810480809
Material	Copper
UPC 12 Digit	781810480809
UPC 14 Digit GTIN	00781810480809

Logistics

Minimum Pack Quantity	15
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)